




EE871



IP55

IP55 Motion Detector Comfort 220/360° Anthracite

Technical Characteristics

Bus system	Without
Fixing mode	surface-mounting
Function	Presence simulation can be used as a single unit, main device or extension unit
Frequency	50/60 Hz
Height of installed product	2.5 m
Dimensions (W x H x D)	91 x 139 x 153 mm
Incandescent bulb power	2300 W
Breaking capacity	16A 250V AC1
Supply voltage	230 V AC
Detection angle	220 / 360 °
Colour	charcoal
Brightness measurement range	5 / 1000 Lux
Maximum Mounting Height	4 m
Connection type	quick connect
Type of contacts	contact floating
Type of connection	with screw terminals
Time delayed range	5s to 30 min
Setting	with potentiometers for fine adjustment of the response brightness, sensitivity and delay time
Component	with fitting material
Protection index IP	IP55
Protection class	isol.class II
Protection	with crawl-under protection
Operating temperature	-20...55 °C
Application, usage	Motion detector