



ESD240

**Contactor 40A, 2NO, 24VAC 50Hz**

**Technical characteristics**

**Architecture**

Number of poles	2 P
-----------------	-----

**Main electrical features**

Rated operational voltage Ue	400 V
Frequency	50 Hz

**Voltage**

Rated insulation voltage	440 V
Rated impulse withstand voltage	4 kV

**Dimensions**

Depth of installed product	60 mm
Height of installed product	85 mm
Width of installed product	54 mm

**Power**

Total power loss under IN	8.6 W
Power dissipation per coil	2.2 W

**Endurance**

Electric endurance in number of cycles	30000
Number of mechanical operations	1000000

**Fluorescent bulbs control**

Max. power with fluorescent parallel lamps	1300 VA
--	---------

**Incandescent bulbs control**

Max. power with incandescent lamps	4000 W
------------------------------------	--------

**Connection**

Number of contacts	2
--------------------	---

**Equipment**

Can be accessorized	Yes
---------------------	-----

**Standards**

European directive WEEE	concerned
-------------------------	-----------

**Safety**

Protection index IP	IP2X
Protection class	isol.class II

**Use conditions**

---

Operating temperature

-10...50 °C