



EEN100



IP20

Twilight switch 1 channel, 1M, wall mounted cell

Technical characteristics

Architecture

Fixing mode	Din-Rail
-------------	----------

Main electrical features

Rated operational voltage Ue	230 V
Frequency	50/60 Hz

Dimensions

Depth of installed product	65 mm
Height of installed product	83 mm
Width of installed product	17.8 mm

Power

Max. power with fluo uncompensated lamps	1000 VA
Power consumed	0.331 VA
Power consumption (operation)	300 mW
Incandescent bulb power	2300 W
Total power loss under IN	0.3 W
Power dissipation per coil	0.3 W

Endurance

Electrical endurance cycles with incandescent lighting	7500
--	------

Power supply

Supply voltage	230 V
----------------	-------

Lighting control

Brightness measurement range	5 / 2000 Lux
------------------------------	--------------

Fluorescent bulbs control

Max. power with fluorescent parallel lamps	1000 VA
Max. power fluo. duo lamp comp. series	1000 W

Incandescent bulbs control

Max. power with incandescent lamps	2300 W
------------------------------------	--------

Installation, mounting

Mounting type	din-Rail
---------------	----------

Connection

Number of contacts	1
--------------------	---

Safety

Protection index IP

IP20