



EG103E



Digital time switch weekly 1 channel Evolution

Technical characteristics

Architecture

| | |
|-------------|----------|
| Fixing mode | Din-Rail |
|-------------|----------|

Functions

| | |
|----------|---------------------|
| Function | Presence simulation |
|----------|---------------------|

Main electrical features

| | |
|------------------------------|-------------------|
| Rated operational voltage Ue | 195 / 230 / 264 V |
| Frequency | 50 Hz |

Dimensions

| | |
|-----------------------------|-------|
| Depth of installed product | 64 mm |
| Height of installed product | 85 mm |
| Width of installed product | 35 mm |

Power

| | |
|----------------------------|-------|
| Power consumed | 6 VA |
| Total power loss under IN | 2 W |
| Power dissipation per coil | 0.5 W |

Battery

| | |
|-----------------------|-------|
| Power reserve [years] | ≈ 5 a |
|-----------------------|-------|

Incandescent bulbs control

| | |
|------------------------------------|--------|
| Max. power with incandescent lamps | 2300 W |
|------------------------------------|--------|

Connection

| | |
|-------------------------------------------|----------------------|
| Connection cross-sect. flexible conductor | 1 / 6mm ² |
| Type of connection | with screw |
| Number of contacts | 1 |
| Type of contacts | 1 changeover |
| Type of connection | with screw terminals |

Settings

| | |
|-----------------------------|-----------|
| Summer / Winter time change | automatic |
| Shortest switching time | 1 mn |
| Type of programming | digital |
| Programming cycle | 1X7D. |

Equipment

| | |
|--------------------|---|
| Number of channels | 1 |
|--------------------|---|

| | |
|------------------------|------------|
| Supply failure reserve | 5 years |
| Use | |
| Cycle | weekly |
| Safety | |
| Protection index IP | IP20 |
| Use conditions | |
| Operating temperature | -5...45 °C |
| Working accuracy | 1,5 |