



EG103E



Digital time switch weekly 1 channel Evolution

Technical characteristics

Architecture

Fixing mode	Din-Rail
-------------	----------

Main electrical features

Rated operational voltage Ue	195 / 230 / 264 V
Frequency	50 Hz

Dimensions

Depth of installed product	64 mm
Height of installed product	85 mm
Width of installed product	35 mm

Power

Power consumed	6 VA
Total power loss under IN	2 W
Power dissipation per coil	0.5 W

Battery

Power reserve [years]	≈ 5 a
-----------------------	-------

Incandescent bulbs control

Max. power with incandescent lamps	2300 W
------------------------------------	--------

Connection

Number of contacts	1
Type of contacts	1 changeover
Type of connection	with screw terminals

Settings

Summer / Winter time change	automatic
Shortest switching time	1 mn
Type of programming	digital
Programming cycle	1X7D.

Equipment

Number of channels	1
Supply failure reserve	5 years

Use

Cycle	weekly
-------	--------

Safety

Protection index IP	IP20
---------------------	------

Use conditions

Operating temperature	-5...45 °C
-----------------------	------------

Working accuracy	1,5
------------------	-----