



EG103V



IP20

## Weekly time switch 1 channel, 12/24V, digital, 2 modules

### Technical characteristics

#### Functions

Function	Presence simulation ; Keylock by means of blocking key ; with pulse function
----------	--

#### Configuration

Switch mode	change-over contact
-------------	---------------------

#### Main electrical features

Rated operational voltage Ue	12 / 24 V
Frequency	50 Hz

#### Dimensions

Depth of installed product	64 mm
Height of installed product	85 mm
Width of installed product	35 mm

#### Power

Power consumed	0.8 VA
Total power loss under IN	2 W
Power dissipation per coil	0.5 W

#### Battery

Charging time of the power reserve in hours	0
---	---

#### Incandescent bulbs control

Max. power with incandescent lamps	2300 W
------------------------------------	--------

#### Connection

Connection cross-sect. flexible conductor	1 / 16mm <sup>2</sup>
Connection cross-sect. rigid cable	1,5 / 10mm <sup>2</sup>
Number of contacts	1
Type of contacts	1 changeover
Type of connection	with screw terminals

#### Settings

Summer / Winter time change	automatic
Shortest switching time	1 mn
Type of programming	digital
Programming cycle	1X7D.

#### Equipment

Number of channels	1
Supply failure reserve	5 years
<b>Use</b>	
Cycle	weekly
<b>Use conditions</b>	
Working accuracy	1,5