



EZN001



Delay on Timer

Technical characteristics

Architecture

Fixing mode	Din-Rail
-------------	----------

Configuration

Switch mode	change-over contact, usable as NC or NO
-------------	---

Main electrical features

Rated operational voltage Ue	12 / 230 V
Frequency	50/60 Hz

Dimensions

Depth of installed product	58 mm
Height of installed product	85 mm
Width of installed product	17.5 mm

Power

Power consumed	15 VA
Power consumption (operation)	15 VA
Total power loss under IN	2 W
Power dissipation per coil	0.5 W

Incandescent bulbs control

Max. power with incandescent lamps	450 W
------------------------------------	-------

Installation, mounting

Mounting type	din-Rail
---------------	----------

Connection

Number of contacts	1
Type of contacts	1 changeover
Type of connection	with screw terminals

Safety

Protection index IP	IP40
---------------------	------

Use conditions

Operating temperature	-10...50 °C
-----------------------	-------------