



EZN001



IP40



Delay on Timer

Technical characteristics

Functions

Function	Functions: On delay, Off delay, single shot leading edge/single shot trailing edge, pulse shaping, flashing symmetrically, contact open/closed
----------	--

Configuration

Switch mode	change-over contact, usable as NC or NO
-------------	---

Main electrical features

Frequency	50/60 Hz
-----------	----------

Dimensions

Depth of installed product	58 mm
Height of installed product	85 mm
Width of installed product	17.5 mm

Power

Power consumed	15 VA
Power consumption (operation)	1.2 W
Total power loss under IN	2 W
Power dissipation per coil	0.5 W

Incandescent bulbs control

Max. power with incandescent lamps	450 W
------------------------------------	-------

Installation, mounting

Mounting type	din-Rail
---------------	----------

Connection

Connection cross-sect. flexible conductor	1 / 6mm ²
Connection cross-sect. rigid cable	1,5 / 10mm ²
Type of connection	with screw
Number of contacts	1
Type of contacts	1 changeover
Type of connection	with screw terminals

Settings

Time delayed range	0.1 s... 10 h
Setting	with 2 potentiometers for setting of delay time

Use conditions

Operating temperature	-20...50 °C
-----------------------	-------------