



EG103V



Weekly time switch 1 channel, 12/24V, digital, 2 modules

Technical characteristics

Architecture

Fixing mode	Din-Rail
-------------	----------

Main electrical features

Rated operational voltage Ue	12 / 24 V
Frequency	50 Hz

Dimensions

Depth of installed product	64 mm
Height of installed product	85 mm
Width of installed product	35 mm

Power

Power consumed	0.8 VA
Total power loss under IN	2 W
Power dissipation per coil	0.5 W

Battery

Charging time of the power reserve in hours	0
---	---

Incandescent bulbs control

Max. power with incandescent lamps	2300 W
------------------------------------	--------

Connection

Connection cross-sect. flexible conductor	1 / 16mm ²
Number of contacts	1
Type of contacts	1 changeover
Type of connection	with screw terminals

Settings

Summer / Winter time change	automatic
Shortest switching time	1 mn
Type of programming	digital
Programming cycle	1X7D.

Equipment

Number of channels	1
Supply failure reserve	5 years

Use

Cycle	weekly
-------	--------

Safety

Protection index IP

IP20

Use conditions

Working accuracy

1,5