



EG203

IP20 

Weekly digital time switch 2 channels, digital, 2 modules

Technical Characteristics

Fixing mode	Din-Rail
Function	Keylock by means of blocking key
Switch mode	2 x change-over contact
Rated operational voltage Ue	195 / 230 / 265 V
Frequency	50 Hz
Supply voltage	230V AC
Depth of installed product	64 mm
Height of installed product	85 mm
Length	85 mm
Width of installed product	35 mm
Dimensions (W x H x D)	35 x 85 x 64 mm
Power consumed	6 VA
Total power loss under IN	4 W
Power dissipation per coil	0.5 W
Breaking capacity	16A 250V AC1
Number of modules	2
Power reserve [years]	≈ 5 a
Charging time of the power reserve in hours	0
Max. power with incandescent lamps	2300 W
Connection cross-sect. flexible conductor	1 / 16mm ²
Connection cross-sect. rigid cable	1,5 / 10mm ²
Type of connection	with screw
Number of contacts	2
Type of contacts	2 changeovers
Type of connection	with screw terminals
Summer / Winter time change	automatic
Shortest switching time	1 mn
Type of programming	digital
Programming cycle	2X7D.
Number of channels	2
Supply failure reserve	5 years
Cycle	weekly
Protection index IP	IP20

Operating temperature

-5...45 °C

Working accuracy

1,5