



EG203E



## Digital time switch weekly cycle 2 channels Evolution

### Technical characteristics

#### Main electrical features

Rated operational voltage Ue	195 / 230 / 265 V
Frequency	50 Hz

#### Dimensions

Depth of installed product	64 mm
Height of installed product	85 mm
Width of installed product	35 mm

#### Power

Power consumed	6 VA
Total power loss under IN	4 W
Power dissipation per coil	0.5 W

#### Battery

Power reserve [years]	≈ 5 a
Charging time of the power reserve in hours	0

#### Incandescent bulbs control

Max. power with incandescent lamps	2300 W
------------------------------------	--------

#### Connection

Type of connection	with screw
Number of contacts	2
Type of connection	with screw terminals

#### Settings

Summer / Winter time change	automatic
Shortest switching time	1 mn
Type of programming	digital
Programming cycle	2X7D.

#### Equipment

Number of channels	2
Supply failure reserve	5 years

#### Use

Cycle	weekly
-------	--------

#### Safety

Protection index IP	IP20
---------------------	------

**Use conditions**

Operating temperature

-5...45 °C

Working accuracy

1,5