



HA358

Load break switch 3P 630A

Technical characteristics

Architecture

Number of poles	3 P
Type of pole	3 P

Main electrical features

Rated operational voltage Ue	380 / 415 V
------------------------------	-------------

Voltage

Rated insulation voltage	1000 V
Rated impulse withstand voltage	8000 V

Dimensions

Depth of installed product	165 mm
Height of installed product	260 mm
Width of installed product	230 mm

Power

Total power loss under IN	92.7 W
---------------------------	--------

Cover, door

Interlockable	Yes
---------------	-----

Connection

Connection cross-sect. flexible conductor	185mm ²
Connection cross-sect. rigid cable	2x300mm ²
Type of connection	Terminal

Equipment

Number of auxiliary contacts as normally closed contact	0
Number of auxiliary contacts as normally open contact	0
Number of auxiliary contacts as change-over contact	0

Standards

Standard text	IEC 60947-3
---------------	-------------

Use conditions

Operating temperature	-20...70 °C
-----------------------	-------------