



EH171



Weekly time switch with reserve 3 modules

Technical characteristics

Architecture

Fixing mode Din-Rail

Functions

Power reserve ≈ 200 h

Configuration

Switch mode change-over contact, usable as NC or NO

Main electrical features

Rated operational voltage U_e 230 V

Frequency 50 Hz

Dimensions

Depth of installed product 60 mm

Height of installed product 90 mm

Width of installed product 54 mm

Power

Power consumed 0.5 VA

Power consumption (operation) 0.5 VA

Total power loss under IN 1 W

Power dissipation per coil 0.5 W

Battery

Charging time of the power reserve in hours 120

Incandescent bulbs control

Max. power with incandescent lamps 900 W

Installation, mounting

Mounting type din-Rail

Connection

Connection cross-sect. flexible conductor 1 / 4mm²

Connection cross-sect. rigid cable 1 / 4mm²

Number of contacts 1

Type of contacts 1 changeover

Type of connection with screw terminals

Settings

Summer / Winter time change	manual
Shortest switching time	2 h
Type of programming	analog
Programming cycle	1X7D.
Equipment	
Number of channels	1
Supply failure reserve	200 h
Use	
Cycle	weekly
Safety	
Protection index IP	IP20
Use conditions	
Operating temperature	-10...45 °C
Working accuracy	1