



HAC406

**Load break switch 4P 63A**

**Technical characteristics**

**Architecture**

Number of poles	4 P
Type of pole	4 P

**Main electrical features**

Rated operational voltage Ue	380 / 415 V
Frequency	50 Hz

**Voltage**

Rated insulation voltage	800 V
Rated impulse withstand voltage	8000 V

**Power**

Total power loss under IN	6 W
---------------------------	-----

**Cover, door**

Interlockable	Yes
---------------	-----

**Installation, mounting**

Tightening torque	3.5 - 3.85 Nm
-------------------	---------------

**Connection**

Connection cross-sect. rigid cable	35mm <sup>2</sup>
Type of connection	with screw

**Equipment**

Number of auxiliary contacts as normally closed contact	0
Number of auxiliary contacts as normally open contact	0
Number of auxiliary contacts as change-over contact	0

**Standards**

European directive WEEE	concerned
-------------------------	-----------

**Safety**

Protection index IP	IP20
---------------------	------

**Use conditions**

Operating temperature	-20...70 °C
-----------------------	-------------