



EH210



Daily time switch without reserve with clock hands, 2 modules

Technical characteristics

Configuration

Switch mode change-over contact, usable as NC or NO

Dimensions

Depth of installed product	58 mm
Height of installed product	90 mm
Width of installed product	36 mm

Power

Power consumed	0.5 VA
Power consumption (operation)	0.5 VA
Total power loss under IN	1 W
Power dissipation per coil	0.5 W

Incandescent bulbs control

Max. power with incandescent lamps	1000 W
------------------------------------	--------

Installation, mounting

Mounting type	din-Rail
---------------	----------

Connection

Connection cross-sect. flexible conductor	1 / 4mm ²
Connection cross-sect. rigid cable	1 / 4mm ²
Number of contacts	1
Type of contacts	1 changeover
Type of connection	with screw terminals

Settings

Summer / Winter time change	manual
Shortest switching time	30 mn
Type of programming	analog
Programming cycle	24H
Setting	Setting via day dial ; Fine setting of time via rotating hand

Equipment

Number of channels	1
Supply failure reserve	without

Use

Cycle	daily
-------	-------

Use conditions

Operating temperature

-10...55 °C

Working accuracy

6 mn / year