



EHN010



Daily time switch 1 channel, 1 module

Technical characteristics

Architecture

| | |
|-------------|----------|
| Fixing mode | Din-Rail |
|-------------|----------|

Main electrical features

| | |
|-----------|----------|
| Frequency | 50/60 Hz |
|-----------|----------|

Dimensions

| | |
|-----------------------------|-------|
| Depth of installed product | 60 mm |
| Height of installed product | 90 mm |
| Width of installed product | 18 mm |

Power

| | |
|-------------------------------|--------|
| Power consumed | 0.5 VA |
| Power consumption (operation) | 0.5 VA |
| Total power loss under IN | 1 W |
| Power dissipation per coil | 0.5 W |

Incandescent bulbs control

| | |
|------------------------------------|-------|
| Max. power with incandescent lamps | 900 W |
|------------------------------------|-------|

Installation, mounting

| | |
|---------------|----------|
| Mounting type | din-Rail |
|---------------|----------|

Connection

| | |
|---|----------------------|
| Connection cross-sect. flexible conductor | 1 / 4mm ² |
| Connection cross-sect. rigid cable | 1 / 4mm ² |
| Number of contacts | 1 |
| Type of contacts | 1 changeover |
| Type of connection | with screw terminals |

Settings

| | |
|-----------------------------|--------|
| Summer / Winter time change | manual |
| Shortest switching time | 15 mn |
| Type of programming | analog |
| Programming cycle | 24H |

Equipment

| | |
|------------------------|---------|
| Number of channels | 1 |
| Supply failure reserve | without |

Use

Cycle

daily

Safety

Protection index IP

IP20

Use conditions

Operating temperature

-10...55 °C

Working accuracy

1