



EHN011

Daily time switch 1 channel, 1 module with reserve

Technical characteristics

Functions

| | |
|---------------|---------|
| Power reserve | ≈ 120 h |
|---------------|---------|

Configuration

| | |
|-------------|------------|
| Switch mode | NO contact |
|-------------|------------|

Main electrical features

| | |
|------------------------------|-------------|
| Rated operational voltage Ue | 230 / 240 V |
| Frequency | 50/60 Hz |

Dimensions

| | |
|-----------------------------|-------|
| Depth of installed product | 60 mm |
| Height of installed product | 90 mm |
| Width of installed product | 18 mm |

Power

| | |
|-------------------------------|--------|
| Power consumed | 0.5 VA |
| Power consumption (operation) | 0.5 VA |
| Total power loss under IN | 1 W |
| Power dissipation per coil | 0.5 W |

Battery

| | |
|---|-----|
| Charging time of the power reserve in hours | 120 |
|---|-----|

Incandescent bulbs control

| | |
|------------------------------------|-------|
| Max. power with incandescent lamps | 900 W |
|------------------------------------|-------|

Installation, mounting

| | |
|---------------|----------|
| Mounting type | din-Rail |
|---------------|----------|

Connection

| | |
|---|----------------------|
| Connection cross-sect. flexible conductor | 1 / 4mm ² |
| Connection cross-sect. rigid cable | 1 / 4mm ² |
| Type of connection | with screw |
| Number of contacts | 1 |
| Type of contacts | 1 changeover |
| Type of connection | with screw terminals |

Settings

| | |
|-----------------------------|--------|
| Summer / Winter time change | manual |
| Shortest switching time | 15 mn |

| | |
|---------------------|----------------------|
| Type of programming | analog |
| Programming cycle | 24H |
| Setting | Setting via day dial |

Equipment

| | |
|------------------------|-------|
| Number of channels | 1 |
| Supply failure reserve | 120 h |

Use

| | |
|-------|-------|
| Cycle | daily |
|-------|-------|

Use conditions

| | |
|-----------------------|-------------|
| Operating temperature | -10...55 °C |
| Working accuracy | 1 |