



EHN011



Daily time switch 1 channel, 1 module with reserve

Technical characteristics

Architecture

Fixing mode	Din-Rail
-------------	----------

Functions

Power reserve	≈ 120 h
---------------	---------

Main electrical features

Rated operational voltage Ue	230 / 240 V
Frequency	50/60 Hz

Dimensions

Depth of installed product	60 mm
Height of installed product	90 mm
Width of installed product	18 mm

Power

Power consumed	0.5 VA
Power consumption (operation)	0.5 VA
Total power loss under IN	1 W
Power dissipation per coil	0.5 W

Battery

Charging time of the power reserve in hours	120
---	-----

Incandescent bulbs control

Max. power with incandescent lamps	900 W
------------------------------------	-------

Installation, mounting

Mounting type	din-Rail
---------------	----------

Connection

Connection cross-sect. flexible conductor	1 / 4mm ²
Connection cross-sect. rigid cable	1 / 4mm ²
Number of contacts	1
Type of contacts	1 changeover
Type of connection	with screw terminals

Settings

Summer / Winter time change	manual
Shortest switching time	15 mn
Type of programming	analog

Programming cycle

24H

Equipment

Number of channels

1

Supply failure reserve

120 h

Use

Cycle

daily

Safety

Protection index IP

IP20

Use conditions

Operating temperature

-10...55 °C

Working accuracy

1