




EHN110



Daily time switch 1 channel, 3 modules

Technical characteristics

Equipment

Number of channels	1
--------------------	---

Frequency

Frequency	50 - 50 Hz
-----------	------------

Power

Power consumption during operation	0.9 W
230 V incandescent and halogen lamp	1,100 W
Power incandescent lamp	900 - 900 W
Power loss at full load	1 W

Functions

Number of function channels	1
-----------------------------	---

Connection

Number of contacts	1
Cross-section flexible conductor	0.5 - 6 mm ²
Cross-section rigid conductor	0.5 - 6 mm ²

Use conditions

Operating temperature	-20 - +55 °C
-----------------------	--------------

Capacity

Number of modules	3
-------------------	---

Dimensions

Height	90 mm
Width	54 mm
Depth	60 mm

Texts

Switch mode	Change-over contact
Installation mode	For mounting on DIN rail
Type of connection	With screw terminals

Electric current

Max. power (cos phi 0,6)	3 A
--------------------------	-----

Endurance

Electrical durability at nominal load in AC1 in operating cycles	50,000
--	--------

Voltage	
Rated operational voltage Ue	230 - 240 V
Settings	
Programme cycles	Programme cycle: 24 hours
Shortest switching time	15 min
Lighting	
LED lamp power	180 W