



EMN001



IP20

## Stair case time lag switch

### Technical characteristics

#### Architecture

Fixing mode Din-Rail

#### Main electrical features

Rated operational voltage  $U_e$  230 V

Frequency 50/60 Hz

#### Electric current

Acceptable current rating with AC1 16 A

#### Dimensions

Depth of installed product 64 mm

Width of installed product 17.5 mm

#### Power

Max. power with fluo uncompensated lamps 3600 VA

Power consumed 1 VA

Total power loss under IN 2 W

Power dissipation per coil 0.25 W

#### Power supply

Supply voltage 230 V

#### Fluorescent bulbs control

Max. power with fluorescent parallel lamps 1000 VA

#### Incandescent bulbs control

Max. power with incandescent lamps 2300 W

#### Installation, mounting

Mounting type din-Rail

#### Connection

Number of contacts 1

Type of contacts 1NO

Type of connection with screw terminals

#### Safety

Protection index IP IP20

#### Use conditions

Operating temperature -10...55 °C