




EMN001



**IP20**

## Stair case time lag switch

### Technical characteristics

#### Main electrical features

Rated operational voltage Ue	230 V
Frequency	50/60 Hz

#### Electric current

Acceptable current rating with AC1	16 A
------------------------------------	------

#### Dimensions

Depth of installed product	64 mm
Width of installed product	17.5 mm

#### Power

Max. power with fluo uncompensated lamps	3600 VA
Power consumed	1 VA
Total power loss under IN	2 W
Power dissipation per coil	0.25 W

#### Power supply

Supply voltage	230 V
----------------	-------

#### Fluorescent bulbs control

Max. power with fluorescent parallel lamps	1000 VA
--	---------

#### Incandescent bulbs control

Max. power with incandescent lamps	2300 W
------------------------------------	--------

#### Installation, mounting

Mounting type	din-Rail
---------------	----------

#### Connection

Connection cross-sect. flexible conductor	1 / 6mm <sup>2</sup>
Connection cross-sect. rigid cable	1,5 / 10mm <sup>2</sup>
Connection type	3 and 4 wires
Number of contacts	1
Type of contacts	1NO

#### Settings

Time delayed range	30s / 10min
--------------------	-------------

#### Safety

Protection index IP	IP20
---------------------	------

#### Use conditions

---

Operating temperature

-10...55 °C