




EPN510



Latching relay 1NO 230V

Technical characteristics

Main electrical features

Rated operational voltage U_e 250 V

Voltage

Rated insulation voltage 250 V

Dimensions

Depth of installed product 63 mm

Height of installed product 83 mm

Width of installed product 17.5 mm

Power

Total power loss under IN 1.2 W

Endurance

Number of mechanical operations 500000

Fluorescent bulbs control

Max. power with fluorescent parallel lamps 900 VA

Incandescent bulbs control

Max. power with incandescent lamps 1800 W

Installation, mounting

Tightening torque 1,6Nm

Connection

Connection cross-sect. flexible conductor 1 / 6mm²

Connection cross-sect. rigid cable 1,5 / 10mm²

Number of contacts 1

Type of contacts 1NO

Standards

Standard text IEC/EN 60669-2

European directive WEEE concerned

Use conditions

Operating temperature -5...40 °C