




EPN540



## Latching relay 4NO 230V

### Technical characteristics

#### Electric current

Rated current	16 A
Quiescent current	6 mA

#### Capacity

Number of modules	2
-------------------	---

#### Connection

Type of contacts	4NO
Cross-section flexible conductor	1 - 6 mm <sup>2</sup>
Cross-section rigid conductor	1.5 - 10 mm <sup>2</sup>
Number of contacts	4

#### Voltage

Command voltage AC	230 - 230 V
Command voltage DC	110 - 110 V
Command voltage 2	110 - 110 V
Command voltage 1	230 - 230 V
Rated insulation voltage Ui	400 V

#### Frequency

Frequency	50 - 60 Hz
-----------	------------

#### Use conditions

Operating temperature	-5 - 40 °C
Storage/transport temperature	-40 - 80 °C

#### Connectivity

Type of connection	Screw terminal
--------------------	----------------

#### Power

Total power loss under IN	4.80 W
Inrush power absorbed	55 VA

#### Dimensions

Height	83 mm
Width	35 mm
Depth	63 mm

#### Lighting

Max. load fluorescent lamp	800 VA
----------------------------	--------