



HDA160U

Moulded Case Circuit Breaker h3 x160 TM ADJ 3P3D 160A 18kA CTC

Technical Characteristics

Neutral position	without neutral
Number of poles	3 P
Type of pole	3P3D
Fixing mode	DIN rail type O or type J
Rated operational voltage Ue	220 / 415 V
Frequency	50/60 Hz
Rated current	160 A
Rated insulation voltage	690 V
Rated impulse withstand voltage	8 kV
Rated service breaking capacity Ics under 400V AC according IEC 60947-2	18 kA
Depth of installed product	68 mm
Height of installed product	130 mm
Width of installed product	75 mm
Total power loss under IN	43.8 W
Short-time delayed tripping	No
Electric endurance in number of cycles	1000
Number of mechanical operations	4000
Interlockable	No
Type of connection	with screw
Number of auxiliary contacts as normally closed contact	0
Number of auxiliary contacts as normally open contact	0
Number of auxiliary contacts as change-over contact	0
Can be accessorized	Yes
Standard text	IEC 60947-2
European directive WEEE	concerned
Protection index IP	IP4X