



ERC325

## Override Contactor 25A, 3NO, 230V~50Hz

### Technical characteristics

#### Architecture

Number of poles	3 P
-----------------	-----

#### Main electrical features

Rated operational voltage $U_e$	400 V
Frequency	50 Hz

#### Voltage

Rated insulation voltage	440 V
Rated impulse withstand voltage	4 kV

#### Dimensions

Depth of installed product	60 mm
Height of installed product	83 mm
Width of installed product	35.75 mm

#### Power

Total power loss under IN	6 W
Power dissipation per coil	1.5 W

#### Endurance

Electric endurance in number of cycles	30000
Number of mechanical operations	100000

#### Fluorescent bulbs control

Max. power with fluorescent parallel lamps	810 VA
--	--------

#### Incandescent bulbs control

Max. power with incandescent lamps	1900 W
------------------------------------	--------

#### Installation, mounting

Tightening torque	1,2Nm
-------------------	-------

#### Connection

Connection cross-sect. flexible conductor	1 / 6mm <sup>2</sup>
Connection cross-sect. rigid cable	1 / 10mm <sup>2</sup>
Type of connection	with screw
Number of contacts	3
Type of contacts	3NO

#### Equipment

Can be accessorized

Yes

---

**Safety**

Protection class

isol.class II

---

**Use conditions**

Operating temperature

-10...50 °C