



HEC251H

**Moulded Case Circuit Breaker h250 4P 70kA 250A LSI**

**Technical Characteristics**

Number of poles	4 P
Rated operational voltage Ue	220 / 690 V
Frequency	50/60 Hz
Rated current	250 A
Rated insulation voltage	800 V
Total power loss under IN	73.2 W
Number of mechanical operations	4000
Number of modules	8
Interlockable	No
Tightening torque	12Nm
Connection cross-sect. flexible conductor	35 / 150mm <sup>2</sup>
Connection cross-sect. rigid cable	35 / 185mm <sup>2</sup>
Type of connection	Terminal
Number of auxiliary contacts as normally closed contact	0
Number of auxiliary contacts as normally open contact	0
Number of auxiliary contacts as change-over contact	0
Can be accessorized	No
Standard text	IEC 60947-2
European directive WEEE	concerned
Protection index IP	IP4X