



HHA048Z

Moulded Case Circuit Breaker h3 x160 TM FIX 1P1D 50A 25kA CTC

Technical characteristics

Electric current

Rated current	50 A
Rated ultimate short-circuit breaking capacity I_{cu} under 240 V AC IEC 60947-2	25 kA
Rated service breaking capacity I_{cs} under 230 V AC according to IEC 60947-2	20 kA
Rated current 10°C according to IEC 60947	61 A
Rated current 15°C according to IEC 60947	59.80 A
Rated current 20°C according to IEC 60947	58.50 A
Rated current 25°C according to IEC 60947	57.10 A
Rated current 30°C according to IEC 60947	55.80 A
Rated current at 35°C according to IEC 60947	54.40 A
Rated current at 40°C according to IEC 60947	52.90 A
Rated current 45°C according to IEC 60947	51.50 A
Rated current 50°C according to IEC 60947	50 A
Rated current 55°C according to IEC 60947	48.40 A
Rated current at 60°C according to IEC 60947	46.80 A
Rated current 65°C according to IEC 60947	45.10 A
Rated current 70°C according to IEC 60947	43.40 A

Architecture

Number of poles	1
Control/operation element	Toggle
Device construction type	Fixed built-in
Neutral position	Without neutral

Tripping

Response time when opening	10 ms
----------------------------	-------

Frequency

Frequency	50 - 60 Hz
-----------	------------

Voltage

Rated impulse withstand voltage U_{imp}	8,000 V
Rated insulation voltage U_i	690 V

Functions

Trip unit	TM F/F
-----------	--------

Power	
Total power loss under IN	5 W
Endurance	
Electric endurance in number of cycles	1,000
Number of mechanical operations	4,000
Safety	
Ingress Protection (IP) class	IP4X
Connection	
Cross-section flexible conductor	4 - 70 mm ²
Cross-section rigid conductor	4 - 95 mm ²
Connectivity	
Type of connection	Screw terminal
Settings	
Thermal protection knob setting xIN	1, 1
Dimensions	
Height	130 mm
Width	25 mm
Depth	68 mm
Compatibility	
Suitable for DIN Rail	Yes
Installation, mounting	
Mounting-/Connection Position	Front
Main electrical attributes	
Magnetic protection trip time	0 - 0 ms