



ESC466

Contactor 63A, 3NO+1NC, 230V~50Hz

Technical characteristics

Architecture

Number of poles	4 P
-----------------	-----

Main electrical features

Rated operational voltage Ue	400 V
Frequency	50 Hz

Voltage

Rated insulation voltage	440 V
Rated impulse withstand voltage	4 kV

Dimensions

Depth of installed product	60 mm
Height of installed product	85 mm
Width of installed product	54 mm

Power

Total power loss under IN	16.5 W
Power dissipation per coil	1.5 W

Endurance

Electric endurance in number of cycles	30000
Number of mechanical operations	1000000

Fluorescent bulbs control

Max. power with fluorescent parallel lamps	2100 VA
--	---------

Incandescent bulbs control

Max. power with incandescent lamps	6500 W
------------------------------------	--------

Installation, mounting

Tightening torque	Coil: 2,5Nm ; Power: 3,5Nm
-------------------	----------------------------

Connection

Connection cross-sect. flexible conductor	1,5 / 16mm ²
Connection cross-sect. rigid cable	1,5 / 25mm ²
Number of contacts	4
Type of contacts	3NO+1NC

Equipment

Can be accessorized	Yes
---------------------	-----

Standards

European directive WEEE	concerned
-------------------------	-----------

Safety

Protection class	isol.class II
------------------	---------------

Use conditions

Operating temperature	-10...50 °C
-----------------------	-------------