



HHA063U

## Moulded Case Circuit Breaker h3 x160 TM ADJ 3P3D 63A 25kA CTC

### Technical characteristics

#### Electric current

Rated current	63 A
Rated ultimate short-circuit breaking capacity Icu under 400 V AC IEC 60947-2	25 kA
Rated ultimate short-circuit breaking capacity Icu under 240 V AC IEC 60947-2	35 kA
Rated service breaking capacity Ics under 230 V AC according to IEC 60947-2	25 kA
Rated service breaking capacity Ics under 400 V AC according to IEC 60947-2	20 kA

#### Architecture

Number of poles	3
-----------------	---

#### Frequency

Frequency	50 - 60 Hz
-----------	------------

#### Voltage

Rated impulse withstand voltage Uimp	8,000 V
Rated insulation voltage Ui	690 V
Rated operational voltage Ue	220 - 415 V

#### Functions

Trip unit	TM A/F
-----------	--------

#### Power

Total power loss under IN	30 W
---------------------------	------

#### Endurance

Electric endurance in number of cycles	1,000
Number of mechanical operations	4,000

#### Safety

Ingress Protection (IP) class	IP4X
-------------------------------	------

#### Connection

Cross-section flexible conductor	4 - 70 mm <sup>2</sup>
Cross-section rigid conductor	4 - 95 mm <sup>2</sup>

#### Installation, mounting

Mounting-/Connection Position	Front
-------------------------------	-------

#### Connectivity

Type of connection	Screw terminal
<b>Settings</b>	
Thermal protection knob setting xIN	0.63, 0.8, 1
<b>Dimensions</b>	
Height	130 mm
Width	75 mm
Depth	68 mm