



EZN002



**IP40**



**Delay off Timer**

**Technical characteristics**

**Architecture**

Fixing mode Din-Rail

**Configuration**

Switch mode change-over contact, usable as NC or NO

**Main electrical features**

Rated operational voltage  $U_e$  12 / 230 V

Frequency 50/60 Hz

**Dimensions**

Depth of installed product 58 mm

Height of installed product 85 mm

Width of installed product 17.5 mm

**Power**

Power consumed 15 VA

Power consumption (operation) 15 VA

Total power loss under IN 2 W

Power dissipation per coil 0.5 W

**Incandescent bulbs control**

Max. power with incandescent lamps 450 W

**Installation, mounting**

Mounting type din-Rail

**Connection**

Number of contacts 1

Type of contacts 1 changeover

Type of connection with screw terminals

**Use conditions**

Operating temperature -10...50 °C