



HHA064Z

## Moulded Case Circuit Breaker h3 x160 TM FIX 4P4D 63A 25kA CTC

### Technical characteristics

#### Architecture

Number of poles	4 P
-----------------	-----

#### Main electrical features

Rated operational voltage Ue	220 / 415 V
Frequency	50/60 Hz

#### Voltage

Rated insulation voltage	690 V
Rated impulse withstand voltage	8 kV

#### Electric current

Rated service breaking capacity Ics under 400V AC according IEC 60947-2	20 kA
-------------------------------------------------------------------------	-------

#### Dimensions

Depth of installed product	68 mm
Height of installed product	130 mm
Width of installed product	100 mm

#### Power

Total power loss under IN	21.3 W
---------------------------	--------

#### Endurance

Electric endurance in number of cycles	1000
Number of mechanical operations	4000

#### Equipment

Number of auxiliary contacts as normally closed contact	0
Number of auxiliary contacts as normally open contact	0
Number of auxiliary contacts as change-over contact	0
Can be accessorized	Yes

#### Standards

Standard text	IEC 60947-2
European directive WEEE	concerned