



EZN004



IP40



Timer

Technical characteristics

Architecture

Fixing mode Din-Rail

Configuration

Switch mode change-over contact, usable as NC or NO

Main electrical features

Rated operational voltage U_e 12 / 230 V

Frequency 50/60 Hz

Dimensions

Depth of installed product 58 mm

Height of installed product 85 mm

Width of installed product 17.5 mm

Power

Power consumed 15 VA

Power consumption (operation) 15 VA

Total power loss under IN 2 W

Power dissipation per coil 0.5 W

Incandescent bulbs control

Max. power with incandescent lamps 450 W

Installation, mounting

Mounting type din-Rail

Connection

Connection cross-sect. flexible conductor 1 / 6mm²

Type of connection with screw

Number of contacts 1

Type of contacts 1 changeover

Type of connection with screw terminals

Safety

Protection index IP IP40

Use conditions

Operating temperature -10...50 °C