




EZN005



IP40



Symmetrical Flasher

Technical characteristics

Functions

Function	Functions: On delay, Off delay, single shot leading edge/single shot trailing edge, pulse shaping, flashing symmetrically, contact open/closed
----------	--

Configuration

Switch mode	change-over contact, usable as NC or NO
-------------	---

Main electrical features

Rated operational voltage U_e	12 / 230 V
---------------------------------	------------

Dimensions

Depth of installed product	58 mm
Height of installed product	85 mm
Width of installed product	17.5 mm

Power

Power consumed	15 VA
Power consumption (operation)	15 VA
Total power loss under IN	2 W
Power dissipation per coil	0.5 W

Incandescent bulbs control

Max. power with incandescent lamps	450 W
------------------------------------	-------

Installation, mounting

Mounting type	din-Rail
---------------	----------

Connection

Connection cross-sect. flexible conductor	1 / 6mm ²
Connection cross-sect. rigid cable	1,5 / 10mm ²
Number of contacts	1
Type of contacts	1 changeover
Type of connection	with screw terminals

Settings

Time delayed range	0.1 s... 10 h
Setting	with 2 potentiometers for setting of delay time

Use conditions

Operating temperature	-20...50 °C
-----------------------	-------------