



HA458

Load break switch 4P 630A

Technical characteristics

Architecture

| | |
|-----------------|-----|
| Number of poles | 4 P |
| Type of pole | 4 P |

Main electrical features

| | |
|------------------------------|-------------|
| Rated operational voltage Ue | 380 / 415 V |
|------------------------------|-------------|

Voltage

| | |
|---------------------------------|--------|
| Rated insulation voltage | 1000 V |
| Rated impulse withstand voltage | 8000 V |

Power

| | |
|---------------------------|--------|
| Total power loss under IN | 92.7 W |
|---------------------------|--------|

Cover, door

| | |
|---------------|-----|
| Interlockable | Yes |
|---------------|-----|

Connection

| | |
|------------------------------------|----------------------|
| Connection cross-sect. rigid cable | 2x300mm ² |
| Type of connection | Terminal |

Equipment

| | |
|---|---|
| Number of auxiliary contacts as normally closed contact | 0 |
| Number of auxiliary contacts as normally open contact | 0 |
| Number of auxiliary contacts as change-over contact | 0 |

Standards

| | |
|---------------|-------------|
| Standard text | IEC 60947-3 |
|---------------|-------------|

Use conditions

| | |
|-----------------------|-------------|
| Operating temperature | -20...70 °C |
|-----------------------|-------------|