



HHA100Z

**Moulded Case Circuit Breaker h3 x160 TM FIX 3P3D 100A 25kA CTC**

**Technical characteristics**

**Electric current**

Rated current	100 A
Rated ultimate short-circuit breaking capacity Icu under 400 V AC IEC 60947-2	25 kA
Rated ultimate short-circuit breaking capacity Icu under 240 V AC IEC 60947-2	35 kA
Rated service breaking capacity Ics under 230 V AC according to IEC 60947-2	25 kA
Rated service breaking capacity Ics under 400 V AC according to IEC 60947-2	20 kA
Rated current 10°C according to IEC 60947	120.50 A
Rated current 15°C according to IEC 60947	118.10 A
Rated current 20°C according to IEC 60947	115.70 A
Rated current 25°C according to IEC 60947	113.20 A
Rated current 30°C according to IEC 60947	110.70 A
Rated current at 35°C according to IEC 60947	108.10 A
Rated current at 40°C according to IEC 60947	105.50 A
Rated current 45°C according to IEC 60947	102.70 A
Rated current 50°C according to IEC 60947	100 A
Rated current 55°C according to IEC 60947	97.10 A
Rated current at 60°C according to IEC 60947	94.10 A
Rated current 65°C according to IEC 60947	91.10 A
Rated current 70°C according to IEC 60947	87.90 A

**Architecture**

Number of poles	3
Control/operation element	Toggle
Device construction type	Fixed built-in
Neutral position	Without neutral

**Tripping**

Response time when opening	10 ms
----------------------------	-------

**Frequency**

Frequency	50 - 60 Hz
-----------	------------

**Voltage**

Rated impulse withstand voltage Uimp	8,000 V
Rated insulation voltage Ui	690 V

<b>Functions</b>	
Trip unit	TM F/F
<b>Power</b>	
Total power loss under IN	39 W
<b>Endurance</b>	
Electric endurance in number of cycles	1,000
Number of mechanical operations	4,000
<b>Safety</b>	
Ingress Protection (IP) class	IP4X
<b>Connection</b>	
Cross-section flexible conductor	4 - 70 mm <sup>2</sup>
Cross-section rigid conductor	4 - 95 mm <sup>2</sup>
<b>Installation, mounting</b>	
Mounting-/Connection Position	Front
<b>Connectivity</b>	
Type of connection	Screw terminal
<b>Settings</b>	
Thermal protection knob setting xIN	1, 1
<b>Dimensions</b>	
Height	130 mm
Width	75 mm
Depth	68 mm
<b>Compatibility</b>	
Suitable for DIN Rail	Yes
<b>Main electrical attributes</b>	
Magnetic protection trip time	0 - 0 ms