



HAC406

Load break switch 4P 63A

Technical characteristics

Architecture

Number of poles	4 P
Type of pole	4 P

Main electrical features

Rated operational voltage Ue	380 / 415 V
Frequency	50 Hz

Voltage

Rated insulation voltage	800 V
Rated impulse withstand voltage	8000 V

Power

Total power loss under IN	6 W
---------------------------	-----

Cover, door

Interlockable	Yes
---------------	-----

Equipment

Number of auxiliary contacts as normally closed contact	0
Number of auxiliary contacts as normally open contact	0
Number of auxiliary contacts as change-over contact	0

Standards

European directive WEEE	concerned
-------------------------	-----------

Safety

Protection index IP	IP20
---------------------	------

Use conditions

Operating temperature	-20...70 °C
-----------------------	-------------