



HCB250H

## Switch X250 3P 250A

### Technical characteristics

#### Architecture

Neutral position	without neutral
Number of poles	3 P
Type of pole	3 P

#### Main electrical features

Rated operational voltage Ue	220 / 415 V
Frequency	50/60 Hz

#### Voltage

Rated insulation voltage	800 V
Rated impulse withstand voltage	8 kV

#### Power

Total power loss under IN	44.1 W
---------------------------	--------

#### Endurance

Electric endurance in number of cycles	10000
Number of mechanical operations	20000

#### Cover, door

Interlockable	Yes
---------------	-----

#### Connection

Connection cross-sect. flexible conductor	35 / 150mm <sup>2</sup>
Connection cross-sect. rigid cable	35 / 185mm <sup>2</sup>

#### Equipment

Number of auxiliary contacts as normally closed contact	0
Number of auxiliary contacts as normally open contact	0
Number of auxiliary contacts as change-over contact	0

#### Standards

Standard text	IEC 60947-3
European directive WEEE	concerned

#### Use conditions

Operating temperature	-25...70 °C
-----------------------	-------------