



HCB251H

**Switch X250 4P 250A**

**Technical characteristics**

**Architecture**

Neutral position	left
Number of poles	4 P
Type of pole	4 P

**Main electrical features**

Rated operational voltage Ue	220 / 415 V
Frequency	50/60 Hz

**Voltage**

Rated insulation voltage	800 V
Rated impulse withstand voltage	8 kV

**Power**

Total power loss under IN	44.1 W
---------------------------	--------

**Endurance**

Electric endurance in number of cycles	10000
Number of mechanical operations	20000

**Cover, door**

Interlockable	Yes
---------------	-----

**Connection**

Connection cross-sect. flexible conductor	35 / 150mm <sup>2</sup>
Connection cross-sect. rigid cable	35 / 185mm <sup>2</sup>
Type of connection	Terminal

**Equipment**

Number of auxiliary contacts as normally closed contact	0
Number of auxiliary contacts as normally open contact	0
Number of auxiliary contacts as change-over contact	0

**Standards**

Standard text	IEC 60947-3
---------------	-------------

**Use conditions**

Operating temperature	-25...70 °C
-----------------------	-------------