



HHB250Z

**Moulded Case Circuit Breaker X250 3P 25kA 250A TM**

**Technical characteristics**

**Architecture**

Number of poles 3 P

**Main electrical features**

Rated operational voltage Ue 220 / 415 V

**Voltage**

Rated insulation voltage 800 V

Rated impulse withstand voltage 8 kV

**Power**

Total power loss under IN 48 W

**Endurance**

Electric endurance in number of cycles 1000

Number of mechanical operations 4000

**Connection**

Connection cross-sect. flexible conductor 35 / 150mm<sup>2</sup>

Connection cross-sect. rigid cable 35 / 185mm<sup>2</sup>

**Equipment**

Number of auxiliary contacts as normally closed contact 0

Number of auxiliary contacts as normally open contact 0

Number of auxiliary contacts as change-over contact 0

**Standards**

Standard text IEC 60947-2

European directive WEEE concerned

**Use conditions**

Operating temperature -25...70 °C