



HCE971H

## Switch h1000 4P 1000A

### Technical characteristics

#### Architecture

Neutral position	left
Number of poles	4 P
Type of pole	4 P

#### Main electrical features

Rated operational voltage Ue	220 / 690 V
Frequency	50/60 Hz

#### Voltage

Rated insulation voltage	800 V
Rated impulse withstand voltage	8 kV

#### Power

Total power loss under IN	186 W
---------------------------	-------

#### Endurance

Electric endurance in number of cycles	4500
Number of mechanical operations	15000

#### Cover, door

Interlockable	Yes
---------------	-----

#### Connection

Type of connection	Terminal
--------------------	----------

#### Equipment

Number of auxiliary contacts as normally closed contact	0
Number of auxiliary contacts as normally open contact	0
Number of auxiliary contacts as change-over contact	0

#### Standards

Standard text	IEC 60947-3
European directive WEEE	concerned

#### Use conditions

Operating temperature	-25...70 °C
-----------------------	-------------