



HMC480T

## MCB 4P 15kA C-80A 6M

### Technical characteristics

#### Architecture

Number of poles	4 P
Curve	C

#### Main electrical features

Rated operational voltage U <sub>e</sub>	415 V
Frequency	50/60 Hz
Type of supply voltage	AC

#### Voltage

Rated insulation voltage	500 V
Rated impulse withstand voltage	6000 V

#### Electric current

Rated short circuit breaking capacity I <sub>cn</sub> under 230V AC according IEC60898-1	15 kA
---	-------

#### Electric current / temperature

Rating current 30°C	80 A
---------------------	------

#### Dimensions

Depth of installed product	70 mm
Height of installed product	90 mm
Width of installed product	106 mm

#### Power

Total power loss under I <sub>N</sub>	25.71 W
---------------------------------------	---------

#### Endurance

Electric endurance in number of cycles	4000
Number of mechanical operations	20000

#### Installation, mounting

Tightening torque	3,5 to 5Nm
-------------------	------------

#### Connection

Type of connection	terminal with tightening compensation system
--------------------	--

#### Standards

Standard text	EN 60898-1 ; IEC 60947-2 ; AS/NZS 60898-1
---------------	---

#### Safety

