



HMD399T

MCB 3P 15kA D-125A 4.5M

Technical characteristics

Architecture

Number of poles	3 P
Type of pole	3 P
Curve	D

Main electrical features

Rated operational voltage U _e	415 V
Frequency	50/60 Hz
Type of supply voltage	AC

Voltage

Rated insulation voltage	500 V
Rated impulse withstand voltage	6000 V

Electric current

Rated short circuit breaking capacity I _{cn} under 230V AC according IEC60898-1	15 kA
---	-------

Electric current / temperature

Rating current 30°C	125 A
---------------------	-------

Dimensions

Depth of installed product	70 mm
Height of installed product	90 mm
Width of installed product	80 mm

Power

Total power loss under I _N	34.93 W
---------------------------------------	---------

Endurance

Electric endurance in number of cycles	4000
Number of mechanical operations	20000

Standards

European directive WEEE	concerned
-------------------------	-----------

Safety

Protection index IP	IP20
---------------------	------