



HEC040H

**Moulded Case Circuit Breaker h250 3P 70kA 40A LSI**

**Technical characteristics**

**Architecture**

Number of poles	3 P
-----------------	-----

**Main electrical features**

Rated operational voltage Ue	220 / 690 V
Frequency	50/60 Hz

**Voltage**

Rated insulation voltage	800 V
Rated impulse withstand voltage	8 kV

**Power**

Total power loss under IN	1.9 W
---------------------------	-------

**Endurance**

Electric endurance in number of cycles	1000
Number of mechanical operations	4000

**Connection**

Type of connection	Terminal
--------------------	----------

**Equipment**

Number of auxiliary contacts as normally closed contact	0
Number of auxiliary contacts as normally open contact	0
Number of auxiliary contacts as change-over contact	0

**Standards**

Standard text	IEC 60947-2
---------------	-------------

**Use conditions**

Operating temperature	-25...70 °C
-----------------------	-------------