



HNG200U

## Moulded Case Circuit Breaker h250 3P 50kA 200A TM

### Technical characteristics

#### Electric current

Rated current	200 A
Rated ultimate short-circuit breaking capacity Icu under 400 V AC IEC 60947-2	50 kA
Rated ultimate short-circuit breaking capacity Icu under 240 V AC IEC 60947-2	85 kA

#### Architecture

Number of poles	3
-----------------	---

#### Frequency

Frequency	50 - 60 Hz
-----------	------------

#### Voltage

Rated impulse withstand voltage Uimp	8,000 V
Rated insulation voltage Ui	800 V

#### Functions

Trip unit	TM A/A
-----------	--------

#### Main electrical attributes

Magnetic protection trip time	0 - 0 ms
-------------------------------	----------

#### Power

Total power loss under IN	31.20 W
---------------------------	---------

#### Endurance

Electric endurance in number of cycles	1,000
Number of mechanical operations	4,000

#### Safety

Ingress Protection (IP) class	IP4X
-------------------------------	------

#### Use conditions

Operating temperature	-25 - 70 °C
-----------------------	-------------

#### Connection

Cross-section flexible conductor	35 - 150 mm²
Cross-section rigid conductor	35 - 185 mm²
Connector/plug type	Terminal

#### Installation, mounting

Nominal tightening torque	12 - 12 Nm
---------------------------	------------

Mounting-/Connection Position	Front
<b>Settings</b>	
Thermal protection knob setting xIN	0.63, 0.8, 1
Adjustment range short-term delayed short-circuit release	0 - 0 A