



HR500

**Earth Leakage Relay 0.03A instantaneous Trip Type A**

**Technical characteristics**

**Main electrical features**

Rated operational voltage Ue 230 V

**Voltage**

Max operating voltage 276 V

**Electric current**

Rated residual operating current 30 mA

**Power**

Power consumed 3 VA

**Installation, mounting**

Tightening torque 1,7Nm

**Connection**

Connection cross-sect. flexible conductor 1 / 2,5mm<sup>2</sup>

Connection cross-sect. rigid cable 1,5 / 4mm<sup>2</sup>

**Standards**

European directive WEEE concerned

**Safety**

Protection index IP IP30

Residual current type A

**Use conditions**

Operating temperature -10...55 °C