



MM501N



**Motor protection circuit breaker 3P 0.1-0.16A ; 0.02/0.03 kW at 230/415V**

**Technical characteristics**

**Architecture**

Number of poles	3 P
Type of pole	3 P

**Main electrical features**

Rated operational voltage $U_e$	690 V
Frequency	50/60 Hz
Type of supply voltage	AC

**Voltage**

Rated insulation voltage	690 V
Rated impulse withstand voltage	6000 V

**Electric current**

Rated service breaking capacity $I_{cs}$ under 400V AC according IEC 60947-2	150 kA
--	--------

**Power**

Total power loss under $I_N$	5.39 W
------------------------------	--------

**Endurance**

Electric endurance in number of cycles	50000
Number of mechanical operations	100000

**Installation, mounting**

Tightening torque	1,7Nm
-------------------	-------

**Connection**

Type of connection	with screw
--------------------	------------

**Equipment**

Can be accessorized	Yes
---------------------	-----

**Standards**

Standard text	IEC 60947-4-1 ; EN 60947-4-1
European directive RoHS	voluntary compliance

**Use conditions**

Operating temperature	-25...55 °C
-----------------------	-------------