



MM510N



**Motor protection circuit breaker 3P 6.3-10A ; 2.2/4 kW at 230/415V**

**Technical characteristics**

**Electric current**

Rated current	10 A
---------------	------

**Dimensions**

Height	140 mm
Width	45 mm
Depth	75 mm

**Architecture**

Control/operation element	Short rotary handle
Number of poles	3

**Voltage**

Rated impulse withstand voltage Uimp	6,000 V
Overvoltage category according to IEC 60947-1	3
Type voltage supply	AC

**Connectivity**

Connection type control and aux contact	Screw terminal
---	----------------

**Equipment**

Sealable	No
With auxiliary contact	No
With thermal protection	Yes

**Safety**

Ingress Protection (IP) class	IP20
-------------------------------	------

**Installation, mounting**

Mounting on	DIN rail
-------------	----------