



MTN110

MCB 1P 6kA B-10A 1M

Technical characteristics

Architecture

Neutral position	not applicable
Number of poles	1 P
Curve	B

Main electrical features

Rated operational voltage U _e	230 / 400 V
Frequency	50/60 Hz
Type of supply voltage	AC

Voltage

Rated insulation voltage	500 V
Rated impulse withstand voltage	4000 V

Electric current

Rated service breaking capacity I _{cs} AC according IEC 60898-1	6 kA
Rated short circuit breaking capacity I _{cn} under 230V AC according IEC60898-1	6 kA

Electric current / temperature

Rating current 30°C	10 A
---------------------	------

Dimensions

Depth of installed product	70 mm
Height of installed product	83 mm
Width of installed product	17.5 mm

Power

Total power loss under I _N	2.75 W
---------------------------------------	--------

Endurance

Electric endurance in number of cycles	4000
Number of mechanical operations	20000

Installation, mounting

Tightening torque	2,8Nm
-------------------	-------

Connection

Type of connection	with screw
--------------------	------------

Equipment

Quick connect	no
Standards	
Standard text	EN 60898-1
Safety	
Protection index IP	IP20
Use conditions	
Operating temperature	-25...70 °C