



HHB200Z

Moulded Case Circuit Breaker X250 3P 25kA 200A TM

Technical characteristics

Architecture

Number of poles 3 P

Main electrical features

Rated operational voltage Ue 220 / 415 V

Voltage

Rated insulation voltage 800 V

Rated impulse withstand voltage 8 kV

Power

Total power loss under IN 38.4 W

Endurance

Electric endurance in number of cycles 1000

Number of mechanical operations 4000

Connection

Connection cross-sect. flexible conductor 35 / 150mm²

Connection cross-sect. rigid cable 35 / 185mm²

Equipment

Number of auxiliary contacts as normally closed contact 0

Number of auxiliary contacts as normally open contact 0

Number of auxiliary contacts as change-over contact 0

Standards

Standard text IEC 60947-2

European directive WEEE concerned

Use conditions

Operating temperature -25...70 °C