



HMC180T

**MCB 1P 15kA C-80A 1.5M**

**Technical characteristics**

**Architecture**

Number of poles	1 P
Type of pole	1 P
Curve	C

**Main electrical features**

Rated operational voltage Ue	240 / 415 V
Frequency	50/60 Hz
Type of supply voltage	AC

**Voltage**

Rated insulation voltage	500 V
Rated impulse withstand voltage	6000 V

**Electric current**

Rated short circuit breaking capacity Icn under 230V AC according IEC60898-1	15 kA
---------------------------------------------------------------------------------	-------

**Electric current / temperature**

Rating current 30°C	80 A
---------------------	------

**Dimensions**

Depth of installed product	70 mm
Height of installed product	90 mm
Width of installed product	27 mm

**Power**

Total power loss under IN	6.18 W
---------------------------	--------

**Endurance**

Electric endurance in number of cycles	4000
Number of mechanical operations	20000

**Standards**

Standard text	EN 60898-1 ; IEC 60947-2 ; AS/NZS 60898-1
European directive WEEE	concerned

**Safety**

Protection index IP	IP20
---------------------	------